INSTALLATION BULLETIN Feed-Thru Boot Assemblies



SPECIFICATIONS

PRODUCT DESCRIPTION

Feed-thru Boot Assemblies feature a one-piece design which dramatically reduces installation time and difficulty. The split one-piece style simplifies mounting by freeing the installer hands in order to position the coax runs, insert the cushion, and tighten the round member adapter clamps without having to hold two separate pieces of the boot in place. Boot assemblies are designed to be fitted onto EP series Entry Panels in wall-roof feed-thru applications. The durable boot is unaffected by ozone, sunlight, aging, or hot and cold extremities. It is designed to meet IP66, ASTM D 2000 and SAE J 200 specifications. Each boot assembly includes boot and two round member adapter clamps. SC-series cushion inserts fit inside the boot assembly to hold the coax in place.

<u>NOTICE</u>

Installation of this product should only be performed by trained, qualified and experienced personnel. Installation instructions for this product should be read thoroughly before installation is performed. The manufacturer and supplier of this product disclaims any liability or responsibility for the results of improper or unsafe installation practice.

MATERIAL LIST

4" (101.6mm) Feed-Thru Boot Assembly

- (1) 4" (101.6mm) Boot
- (1) #80 or #88 Hose Clamp
- (1) #64 Hose Clamp
- (1) Cushion Insert*

5" (127mm) Feed-Thru Boot Assembly

- (1) 5" (127.mm) Boot
- (1) #88 Hose Clamp
- (1) #64 Hose Clamp
- (1) Cushion Insert*

*Cushion Inserts available in specified models.

REQUIRED TOOLS

• (1) 5/16" Nut Driver or Flathead Screwdriver





Visit us at: www.fimoworld.com - E-mail us at: customersupportUSA@fimoworld.com - "Building Sustainable Innovation" Call us at U.S. Telephone: 1 (203) 759-3744